


GROUNDING BUSBAR, W/INSULATORS AND BRACKETS, EE, 152 MM X 51 MM X 6.4 MM, TINNED

CATALOGUSNUMMER

EGBA14206EET



Proper bonding is essential to create an equipotential plane between service grounds and equipment during fault and transient conditions. This equipotential plane provides a near-zero voltage differential, and serves to protect people and equipment during these events. The grounding busbar is the most popular bonding product in use today.

CERTIFICATIONS



KENMERKEN

Provides a convenient, single-point grounding and bonding location

Conductors are welded to the bar using a nVent ERICO Cadweld exothermic connection or are mechanically fastened by using lugs

Custom bars can be designed and manufactured to customer specifications

PRODUCTKENMERKEN

Material: Copper

Busbar Configuration: Busbar, Insulators and Brackets

Hole Pattern: EE Hole Pattern

Mounting Hole Size: 11.1mm

Length (L): 152mm

Width (W): 51mm

Thickness (T): 6.4mm

Tin Plating: Yes

Pigtail Included: No

ADDITIONAL PRODUCT DETAILS


Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.

Additional configurations are available by special order. Note special orders may incur additional lead time.

EGB-A-14-4-12-CC-T-1T-K		
EGB	ERICO Grounding Busbar Designation	
A	Configuration	A: Busbar, Insulators and Brackets B: Busbar and Brackets C: Busbar Only D: Busbar and Insulators
14	Thickness (")	14: 1/4" · 38: 3/8" · 12: 1/2"
4	Width (")	
12	Length (")	Rounded to the nearest inch, 144" max
CC	Hole Pattern	Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.
T*	Tin Plating	
1T*	ERICO Cable Code	1K: #4 Sol Tin · 1T: #2 Sol Tin 2C: 1/0 · 2G: 2/0 · 2L: 3/0 · 2Q: 4/0 2V: 250 kcmil · 3D: 350 kcmil · 3Q: 500 kcmil · 4L: 750 kcmil
K*	Pigtail Length (")	A:1 · B:2 · C:3 · D:4 · E:5 · F:6 · G:7 · H:8 · J:9 · K:10 · L:12 · M:14 · N:16 P:18 · Q:20 · R:22 · S:24 · T:26 · U:28 · V:30 · W:32 · X:34 · Y:36 · Z:38

* Empty if none

DIAGRAMS



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER