


TRC FOUR POLE DISTRIBUTION BLOCK, 630 A



CERTIFICATIONS



KENMERKEN

Transparent protection cover

Bolts included for output connections

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

SPECIFICATIES

Table 1/3

Catalogusnummer	Article Number	Peak Short Circuit Current (I _{pk})	Materiaal	Short Term Withstand Current (I _{cw}) 1s	Line Side Number of Connections	Load Side Number of Connections
TRC-630A	563190	84kA	Copper, Glass Fibre Reinforced Polyamide, Plexiglass	52kA	1	8

Table 2/3

Catalogusnummer	Article Number	Formaat draad (TS)	Max Working Voltage, IEC (Ui)	Formaat gat (HS)	Hoogte (H)	Breedte (W)
TRC-630A	563190	M8	1000	10mm	338 – 390mm	340mm


Table 3/3

Catalogusnummer	Article Number	Diepte (D)	A	Eenheid gewicht (metrisch)	Flammability Rating	Conform
TRC-630A	563190	60mm	290mm	4.8kg	UL® 94V-0	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

DIAGRAMS



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER