


BD TWO POLE DISTRIBUTION BLOCK, 100/125 A



CERTIFICATIONS



CARACTERÍSTICAS

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Input separated from outputs

Wiring with or without terminal

Easily clips onto DIN rail or mounts to panel with screws

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

ESPECIFICAÇÕES

Table 1/4						
Número de catálogo	Article Number	Max Current Rating, IEC	Peak Short Circuit Current (I _{pk})	Line Side Stranded Wire Size - Ferrule	Line Side Compact Stranded Wire Size	Short Term Withstand Current (I _{cw}) 1s
BD-100-125A	563800	125A	30kA	10 – 35mm ²	10 - 35 mm ²	4.5kA
BD-100-125AL	563810	125A	25kA	10 – 35mm ²	10 - 35 mm ²	4.5kA

Table 2/4						
Número de catálogo	Article Number	Line Side Number of Connections	Load Side Number of Connections	Load Side Compact Stranded Wire Size	Load Side Stranded Wire Size - Ferrule	Max Working Voltage, IEC (U _i)
BD-100-125A	563800	1	6	(5) 2,5 - 6 mm ² , (1) 10 - 25 mm ²	(5) 1,5 – 6 mm ² , (1) 6 – 16 mm ²	690V
BD-100-125AL	563810	1	14	(11) 2,5 - 6 mm ² , (3) 10 - 25 mm ²	(11) 1,5 – 6 mm ² , (3) 6 – 16 mm ²	690V

Table 3/4						
Número de catálogo	Article Number	Altura (H)	Largura (W)	Profundidade (D)	Peso unitário	Flammability Rating
BD-100-125A	563800	50mm	94mm	50mm	0.16kg	UL® 94V-0
BD-100-125AL	563810	50mm	162mm	50mm	0.27kg	UL® 94V-0


Table 4/4		
Número de catálogo	Article Number	Em conformidade com
BD-100-125A	563800	IEC® 60947-7-1
BD-100-125AL	563810	IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER