


BD TWO POLE DISTRIBUTION BLOCK, 80/100 A



CERTIFICATIONS



CARACTERÍSTICAS

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Wiring with or without terminal

Easily clips onto DIN rail or mounts to panel with screws

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

ESPECIFICAÇÕES

Table 1/4

Número de catálogo	Article Number	Max Current Rating, IEC	Peak Short Circuit Current (Ipk)	Line Side Stranded Wire Size - Ferrule	Line Side Compact Stranded Wire Size	Short Term Withstand Current (Icw) 1s
--------------------	----------------	-------------------------	----------------------------------	--	--------------------------------------	---------------------------------------

BD-80-100A	563900	100A	20kA	10 – 25mm ²	10 - 25 mm ²	4.5kA
BD-80-100AL	563910	100A	20kA	10 – 25mm ²	10 - 25 mm ²	4.5kA

Table 2/4

Número de catálogo	Article Number	Line Side Number of Connections	Load Side Number of Connections	Load Side Compact Stranded Wire Size	Load Side Stranded Wire Size - Ferrule	Max Working Voltage, IEC (Ui)
BD-80-100A	563900	1	6	(3) 1,5 - 4 mm ² , (3) 2,5 - 6 mm ²	(3) 0,75 – 4 mm ² , (3) 1,5 – 6 mm ²	500V
BD-80-100AL	563910	2	13	(6) 1,5 - 4 mm ² , (7) 2,5 - 6 mm ²	(6) 0,75 – 4 mm ² , (7) 1,5 – 6 mm ²	500V

Table 3/4

Número de catálogo	Article Number	Altura (H)	Largura (W)	Profundidad e (D)	Peso unitário	Flammability Rating
BD-80-100A	563900	50mm	64mm	50mm	0.11kg	UL® 94V-0
BD-80-100AL	563910	50mm	130mm	50mm	0.21kg	UL® 94V-0

Table 4/4

Número de catálogo	Article Number	Em conformidade com
BD-80-100A	563900	IEC® 60947-7-1
BD-80-100AL	563910	IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.


Design Guideline for Distribution Blocks, Power Blocks and Power Terminals

Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C

Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47

*environment around the terminal blocks inside the enclosure

DIAGRAMS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER