

TD COMPACT FOUR POLE DISTRIBUTION BLOCK, 80/100 A



CERTIFICATIONS



FUNKSJONER

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

Solid bars provide reliability

Wiring with or without terminal

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

SPESIFIKASJONER

Materiale: Thermoplastic; Brass

Table 1/4

Katalognummer	Article Number	Max Current Rating, IEC	Peak Short Circuit Current (I _{pk})	Line Side Stranded Wire Size - Ferrule	Line Side Compact Stranded Wire Size	Short Term Withstand Current (I _{cw}) 1s
TD-80-100A	563920	100A	20kA	10 – 25mm ²	10 - 25 mm ²	4.5kA
TD-80-100AL	563930	100A	20kA	10 – 25mm ²	10 - 25 mm ²	4.5kA
TD-80-100ALL	563940	100A	20kA	10 – 25mm ²	10 - 25 mm ²	4.5kA

Table 2/4

Katalognummer	Article Number	Line Side Number of Connections	Load Side Number of Connections	Load Side Compact Stranded Wire Size	Load Side Stranded Wire Size - Ferrule	Max Working Voltage, IEC (Ui)
TD-80-100A	563920	1	6	(3) 1,5 - 4 mm ² , (3) 2,5 - 6 mm ²	(3) 0,75 – 4 mm ² , (3) 1,5 – 6 mm ²	500V
TD-80-100AL	563930	2	9	(4) 1,5 - 4 mm ² , (5) 2,5 - 6 mm ²	(4) 0,75 – 4 mm ² , (5) 1,5 – 6 mm ²	500V
TD-80-100ALL	563940	2	13	(6) 1,5 - 4 mm ² , (7) 2,5 - 6 mm ²	(6) 0,75 – 4 mm ² , (7) 1,5 – 6 mm ²	500V

Table 3/4

Katalognummer	Article Number	Høyde (H)	Bredde (W)	Dybde (D)	Komponentvækt	Flammability Rating
TD-80-100A	563920	90mm	64mm	50mm	0.21kg	UL® 94V-0
TD-80-100AL	563930	90mm	100mm	50mm	0.31kg	UL® 94V-0
TD-80-100ALL	563940	90mm	130mm	50mm	0.4kg	UL® 94V-0

Table 4/4


Katalognummer	Article Number	Samsvarer med
TD-80-100A	563920	IEC® 60947-7-1
TD-80-100AL	563930	IEC® 60947-7-1
TD-80-100ALL	563940	IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Our powerful portfolio of brands:

nVent.com **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF**

TRACER