





DESIGN_(PDU)
ENGINEERING




RECEPTACLE

C13/C15 COMBO
10A, 250V MAX
RATED OUTPUT

C13/C15/C19 COMBO
16A, 250V MAX
RATED OUTPUT


STANDARD
RECEPTACLES

RECEPTACLE



C13/C15/C19 COMBO
16A, 250V MAX
RATED OUTPUT

RECEPTACLE



C13/C15 COMBO
10A, 250V MAX
RATED OUTPUT

INPUT PLUG

(DEFAULT)



IEC 60309, 3P+N+E,6H
IP44(SPLASHPROOF)
DUAL RATED 30A(24 DERATED)/32A
346-415V MAX RATED INPUT


OPTIONAL



IEC 60309, 3P+N+E,6H
IP67(WATERTIGH)
DUAL RATED 30A(24 DERATED)/32A
346-415V MAX RATED INPUT

MOUNTING BUTTON

BUTTON MOUNTING SCREW
(INCLUDED)



- NOTES :
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE :

Advantage Series
Basic

PROJECT :

enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN
MILLIMETERS & TOLERANCES ARE:

X	±1	MM	X"	±1"
X.X	±0.5	MM	X.X"	±0.5"
X	±0.20	MM		
Ø X.X	±0.3	MM		
Ø X.XX	±0.10	MM		

BRACKETED DIMENSIONS ARE IN
INCHES FOR REFERENCE ONLY

⊕ THRID ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

PART NO:
EB0450-WXYZ_DA

REV.
E3

DRAWN BY: LRF

2022/05/23

ENGINEER: LJB

2023/02/09

APPROVED BY: Hanson

2023/02/09

SCALE : N/A

SHEET
2 OF 3
SIZE:
A3

