









DESIGN^(PDU)
ENGINEERING



FULLY DEPRESS RELEASE BUTTON PRIOR TO INSTALLING PLUG FOR EASIEST INSTALL
(PLUG CAN ALSO BE INSERTED WITHOUT DEPRESSING RELEASE BUTTON)
TO UNLOCK, FULLY DEPRESS RELEASE BUTTON AND REMOVE PLUG



LOCKING COMBO OUTLET

STANDARD RECEPTACLES

RECEPTACLE

IEC 60320 C13, C15
MAX RATED OUTPUT 10A, 250V

IEC 60320 C13, C15, C19, C21
MAX RATED OUTPUT 16A, 250V


INPUT PLUG

(DEFAULT)


IEC 60309, 2P 3W, 6H
IP44 (SPLASHPROOF)
32A, 200-250V MAX RATED INPUT

OPTIONAL

IEC 60309, 2P 3W, 6H
IP67 (WATERTIGHT)
32A, 200-250V MAX RATED INPUT



- Critical Alarm Alerts**
- PDU Alarm
 - Cascade Error
 - Environmental Alarm
 - Security Alarm
 - Circuit Breaker Alarm
- Source Color Coding**
(User Selected Option)
- User Interactive Display**
(for setup and detailed information)
- 10/100 Ethernet Port**
(for redundancy and Ethernet cascading)
- Digital Sensor Port 2**



- NOTES:
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

enLOGIC by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

	E1	INITIAL DRAFT REVIEW	2022/08/08	LRF
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
REVISIONS				
TITLE:		Advantage Series Metered Switched	UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X. ±1 MM X° ±1° X.X ±0.5 MM X.X° ±0.5° X.XX ±0.20 MM ØX.X ±0.3 MM ØX.XX ±0.10 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ⊕ THRID ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994	
PROJECT:		enLOGIC	PART NO: EN2380-WXYZ_DA DRAWN BY: LRF ENGINEER: LJB APPROVED BY: Hanson	
			SCALE: N/A	REV. E1 2022/08/08 2022/08/08 2022/08/08
				SHEET 2 OF 3 SIZE: A3

enLOGIC

RACK Power Distribution Unit

Metered Switched

CE

UK

Made In XXXXX

CIS Global LLC
1601 W COMMERCE
CT TUCSON,
AZ 85746

SKU#: EN2380-WXYZ

Model #: EP121032-0070-L

INPUT: 200-240VAC,1PHASE,50/60Hz,32A

OUTPUT: C13/C15 LOCKING; 200-240VAC, 10A per outlet

C13/C15/C19 LOCKING; 200-240VAC, 16A max per outlet

32A Total

MAC0 Address:XX-XX-XX-XX-XX-XX

MAC1 Address:XX-XX-XX-XX-XX-XX

Barcode

EN2380-WXYZ

Barcode

Serial Number

XXXXXXXXXX

NOTES:

1. INTERNAL WIRING

WIRE TYPE: UL AWM 1015,10 & 12 & 18 AWG

LINE 1/R/X COLOR: BROWN

NEUTRAL COLOR: BLUE

EARTH GROUND COLOR: GREEN

2. FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

DESIGN(PDU)
ENGINEERING

COMPLIANCE LABEL

INTERNAL WIRING SCHEMATIC DIAGRAM

NOTES:

- 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
- 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
- 3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

enLOGIC

by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

	E1	INITIAL DRAFT REVIEW		2022/08/08	LRF
ECN/ECO	REV.	DESCRIPTION		DATE	APPROVED
REVISIONS					
TITLE: Advantage Series Metered Switched		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X. ±1 MM X.X ±0.5 MM X.XX ±0.20 MM ØX.X ±0.3 MM ØX.XX ±0.10 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ⊕ THRID ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994	PART NO: EN2380-WXYZ_DA		REV. E1
			DRAWN BY: LRF		2022/08/08
			ENGINEER: LJB		2022/08/08
			APPROVED BY: Hanson		2022/08/08
PROJECT: enLOGIC		SCALE:N/A		SHEET 3 OF 3	
				SIZE: A3	