


ELECTRICAL EARTH BAR, BARE, 22 CONNECTIONS, 2 NUMBER OF DISCONNECTS, 1,400 MM

KATALOGNUMMER

EEB22C506D2A



DESIGN

Provides a convenient, single-point grounding and bonding location

Busbars with disconnect links allow for convenient testing of the earth termination system

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

Includes halogen-free polyamide insulators, stainless steel (EN 1.4401) hardware and mounting brackets

Custom bars can be designed and manufactured to customer specifications

PRODUKTATTRIBUT

Uppfyller kraven enligt: IEC® EN 62561-1:2017 Class H

Material: Copper

Finish: Bare

Antal anslutningar: 22

Antal frånkopplingar: 2

Gångstorlek (TS): M10

Höjd (H): 94mm

Längd (L): 1400mm

Bredd 1 (W1): 100mm

Bredd 2 (W2): 50mm

Tjocklek (T): 6mm


A: 50mm

Enhetsvikt: 6.55kg

ADDITIONAL PRODUCT DETAILS

Tinned finish is 8 microns according to ASTM B545 Service Class "C" for corrosive environments.

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER