


SBLT-250 LUG-TO-TUNNEL POWER TERMINAL



CERTIFICATIONS



DESIGN

Tinned copper block allows for copper or aluminum conductor connections

Accessible studs and tunnels allow for easy connection of nVent ERIFLEX Flexibar and other conductors

Design allows for visual inspection of conductor and confirmation of connection

Adjustable transparent cover

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

SBLEC Power Terminals Fixing Accessory required for direct panel mount

RoHS compliant

Halogen free

SPECIFIKATIONER

Table 1/5

Katalognummer	Article Number	Finish	Max Current Rating, IEC	Max Current Rating, UL/CSA	Högsta statiska kortslutningssström (SCCR)	Peak Short Circuit Current (I _{pk})
SBLT-250	561140	Tinned	350A	300A	100kA	30kA

Table 2/5

Katalognummer	Article Number	Material	Number of Stud Connections	Stud Connection Conductor Width	Short Term Withstand Current (I _{cw}) 1s	Stud Connection Wire Size
SBLT-250	561140	Copper, Thermoplastic	1	20 – 24 mm	8.4kA	#6 - 250 kcmil

Table 3/5

Katalognummer	Article Number	Stud Connection Compact Stranded Wire Size	Number of Tunnel Connections	Max Working Voltage, IEC (U _i)	Max Working Voltage, UL (V _{in})	Tunnel Connection Wire Size - Ferrule
SBLT-250	561140	10 – 120 mm ²	2	1000, 1500	1000	(2) 10 – 35 mm ²

Table 4/5

Katalognummer	Article Number	Tunnel Connection Compact Stranded Wire Size	Tunnel Connection Wire Size	Höjd (H)	Bredd (W)	Djup (D)
SBLT-250	561140	(2) 10 – 50 mm ²	(2) #8 – 1/0	205.7mm	52.3mm	65mm

Table 5/5


Katalognummer	Article Number	A	Enhetsvikt	Flammability Rating	Certification Details	Uppfyller kraven enligt
SBLT-250	561140	108mm	0.27kg	UL® 94V-1	UL® 1059	IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Power terminal connections are interchangeable and can be used as line side or load side connections.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER