

GUIDE RAIL WITH CODING FOR COMPACTPCI/ VME64X, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



功能

新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定

稳定性显著提高, 得益于优化设计和高质量材料 (PC)

提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3

“无卤素”, 符合 IEC 61249-2-21 标准

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中

可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求

可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点

存储温度：从 -40 °C.. 130 °C

技术参数

Table 1/2

物料号	类型	适用于	Board Depth	材料	颜色	包装数量
-----	----	-----	-------------	----	----	------

64568-089	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯	红色	1
64568-090	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯	灰色	1
64568-085	编码	插箱, 仪器箱, 19 英寸机箱, 系统	70mm	聚碳酸酯	红色	1
64568-086	编码	插箱, 仪器箱, 19 英寸机箱, 系统	70mm	聚碳酸酯	灰色	1
64568-091	编码	插箱, 仪器箱, 19 英寸机箱, 系统	220mm	聚碳酸酯	红色	1
64568-092	编码	插箱, 仪器箱, 19 英寸机箱, 系统	220mm	聚碳酸酯	灰色	1
64568-111	编码	插箱, 仪器箱, 19 英寸机箱, 系统	220mm	聚碳酸酯, 铝	红色, 银色	1
64568-109	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯, 铝	红色, 银色	1
64568-110	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯, 铝	灰色, 银色	1
64568-112	编码	插箱, 仪器箱, 19 英寸机箱, 系统	220mm	聚碳酸酯, 铝	灰色, 银色	1
24568-356	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯	红色	10
24568-357	编码	插箱, 仪器箱, 19 英寸机箱, 系统	70mm	聚碳酸酯	红色	10
24568-358	编码	插箱, 仪器箱, 19 英寸机箱, 系统	160mm	聚碳酸酯	灰色	10
24568-360	编码	插箱, 仪器箱, 19 英寸机箱, 系统	70mm	聚碳酸酯	灰色	10
24568-331	编码	插箱, 仪器箱, 19 英寸机箱, 系统	280mm	聚碳酸酯, 铝	红色, 银色	10
24568-332	编码	插箱, 仪器箱, 19 英寸机箱, 系统	340mm	聚碳酸酯, 铝	红色, 银色	10
24568-341	编码	插箱, 仪器箱, 19 英寸机箱, 系统	280mm	聚碳酸酯, 铝	灰色, 银色	10
24568-342	编码	插箱, 仪器箱, 19 英寸机箱, 系统	340mm	聚碳酸酯, 铝	灰色, 银色	10

Table 2/2

物料号	符合	凹槽宽度	表面处理
64568-089	EN 45545-2	2	
64568-090	EN 45545-2	2	
64568-085	EN 45545-2	2	
64568-086	EN 45545-2	2	
64568-091	EN 45545-2	2	
64568-092	EN 45545-2	2	
64568-111	EN 45545-2	2.5	
64568-109	EN 45545-2	2.5	
64568-110	EN 45545-2	2.5	
64568-112	EN 45545-2	2.5	
24568-356	EN 45545-2	2	
24568-357	EN 45545-2	2	
24568-358	EN 45545-2	2	
24568-360	EN 45545-2	2	
24568-331	EN 45545-2	2.5	阳极氧化
24568-332	EN 45545-2	2.5	阳极氧化
24568-341	EN 45545-2	2.5	阳极氧化
24568-342	EN 45545-2	2.5	

ADDITIONAL PRODUCT DETAILS

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.